

Cabinet Lift Series

Stay Lift Systems Cushion Closing



Features

- Maximise the cabinet storage space
- · Cushion closing
- · Adjustable to the weight of your door
- Cabinet heights between 160mm 400mm
- · Minimum cabinet depth of 100mm
- Quick and simple installation with quick disconnect
- · Elegant chrome finish


- · Kitchen & Bath Cabinets
- Store Fixtures
- Architectural Millwork
- Office Furniture
- Medical Equipment Storage

Cabinet Lift Series



Stay Lift Systems Cushion Closing


Cabinet and Door Mounting Plate Locations



Use 2 chipboard screws (609.1x00) for wooden fronts.

Use 2 counter sunk self tapping screws for wide alu frames.

FAo	Upper front overlay	
SFA	Front overlay of the side panel	
MD	Mounting plate spacing	
K	Cranking of hinge arm	
	Straight hinge arm – 0 mm	
	Cranked hinge arm – 9.5 mm	
	Double cranked arm – 18 mm	
() Internal cabinet depth 10		



H = 13	7 + MD + K + SOB	
MD	Mounting plate spacing	
K	Cranking of hinge arm	
	Straight hinge arm – 0 mm	
	Cranked hinge arm – 9.5 mm	
	Double cranked arm – 18 mm	
SOB	Top panel thickness	
() Internal cabinet depth 100		

- Standard hinge and plate drilling

Ordering

Cabinet Door Lift Mechanism Stay Lift

Part Number: 240-1619

Face Frame Mounting Plate Clip-On

Part Number: 240-1637

Note: To be used in conjunction with two soft closing hinges and plates.

FORCE FACTOR

Cabinet height in mm X Door Weight in Kgs (include handle weight)

1 PCS	400-1600
2 PCS	800-3200











