


AvanTech YOU double walled drawer system

- ▶ Quadro YOU drawer runner with Silent System
- ▶ For AvanTech YOU or wooden drawers

11 B Quadro YOU drawer runner with Silent System



- ▶ Full extension runner for combining with AvanTech YOU system drawer or wooden drawer with catches
- ▶ Integrated Silent System
- ▶ Optionally upgradable with Push to open Silent
- ▶ Load capacity 30 kg
- ▶ Load capacity to EN 15338, Level 3
- ▶ Galvanised steel


Load class M (30 kg)

Nominal length mm	Order no.	PU	Order no. / mounting side		PU
			left	right	
270	9 256 883	1 pair			
300	9 256 884	1 pair			
350	9 256 886	1 pair			
400			9 256 864	9 256 865	20 ea.
450			9 256 868	9 256 869	20 ea.
500			9 256 872	9 256 873	20 ea.
550			9 256 876	9 256 877	20 ea.
600	9 256 896	1 pair			

AvanTech YOU double walled drawer system

- Quadro YOU drawer runner with Silent System
- For AvanTech YOU or wooden drawers


Lengthwise cross-section



Installation dimensions with Silent System / Push to open Silent

Nominal length mm	Hole spacing b1 mm	Drawer Minimum cabinet body depth mm	Internal drawer / Minimum cabinet body depth mm
270	160	273	282
300	160	303	312
350	224	353	362
400	224	403	412
450	256	453	462
500	256	503	512
550	256	553	562
600	256	603	612

Quadro YOU catch




- For using Quadro YOU with wooden drawers
- Height adjustment up to + 3 mm
- Plastic

Cabinet side	Order no.	PU
left	9 257 260	100 ea.
right	9 257 261	100 ea.

AvanTech YOU double walled drawer system

► Push to open Silent opening system for Quadro YOU

Push to open Silent opening system for Quadro YOU



- Can be used with AvanTech YOU system drawer on Quadro YOU drawer runner with Silent System
- Optional synchronisation possible

Set comprises:

- 1 Push to open Silent unit, left and right
- 1 activator, left and right
- 2 adapters for synchronisation

Total weight kg	Load class Quadro kg	Nominal length mm	Order no.	PU
8 - 20	30 kg	270 - 600	9 257 895	1 set
10 - 30	30 kg	350 - 600	9 257 896	1 set

Recommendation for drawer (front panel height up to approx. 150 mm, light duty loading)*

Nominal length mm	Nominal width mm												
	275	300	350	400	450	500	550	600	700	800	900	1000	1200
270													
300													
350													
400													
450													
500													
550													
600													

Recommendation for drawer (front panel height up to approx. 300 mm, medium duty loading)*

Nominal length mm	Nominal width mm												
	275	300	350	400	450	500	550	600	700	800	900	1000	1200
270													
300													
350													
400													
450													
500													
550													
600													

Recommendation drawer, heavy duty (front panel height up to approx. 300 mm, heavy duty loading, e.g. with stacks of plates)*

Nominal length mm	Nominal width mm												
	275	300	350	400	450	500	550	600	700	800	900	1000	1200
270													
300													
350													
400													
450													
500													
550													
600													

Order no. Push to open Silent:

9 257 895


9 257 896

* Recommendations for standard applications (front panel 19 mm chipboard, normal household loading), please refer to our online configurator to get more exact recommendations for customer chosen front panel dimensions and materials.

AvanTech YOU double walled drawer system

► Push to open Silent opening system for Quadro YOU

Optional synchronisation for Push to open Silent



- Recommended for cabinet body widths > 600 mm

Synchronisation bar:


- For cutting to length
- Length 2000 mm
- Aluminium anodised

Connector:

- For connecting 2 synchronisation bars
- Plastic, grey

Article	Order no.	PU
1 Synchronisation bar	9 236 718	1 ea.
2 Connectors	9 221 295	20 ea.


Optional multisynchronisation for Push to open Silent



- Synchronisation bar for cutting to length, 2000 mm
- Connector for minimising offcut waste
- Recommended for cabinet body widths > 600 mm; can be used from 275 mm
- Aluminium, anodised, grey plastic

Article	Order no.	PU
1 Synchronisation bar	9 236 718	1 ea.
3 Connectors	9 278 452	20 ea.


Optional flexible adapter for synchronisation



- For use in conjunction with lowered drawer runners (angled fronts)
- Replaces the adapter for synchronisation in the Push to open Silent set

Order no.	PU
9 262 213	20 ea.

Optional synchronisation deflector for Push to open Silent



- For moving the synchronisation bar by 50, 90 or 140 mm

Set comprises:

- 2 housings
- 2 adapters for Push to open unit
- 2 adapters for synchronisation bar

Order no.	PU
9 278 453	1 set

Information

► AvanTech YOU drawer	268 – 283	► Actro YOU / Quadro YOU drawer runners	300 – 307
► AvanTech YOU Inlay	284 – 286	► Push to open Silent	302 – 303, 306 – 307
► Rear panel options	288 – 289	► Quality criteria	544
► Design options / accessories	294 – 298		



hettich.com/short/370f63


AvanTech YOU double walled drawer system

► Example application with narrow base unit



- Cabinet body height 750 mm max.
- Cabinet body width 300 mm max.
- Actro YOU / Quadro YOU drawer runner is required on the left and right, mounted diagonally
- Total load capacity 20 kg max.
- Other configurations are also possible

Example application



No.	Application	see pages
1	AvanTech YOU drawer	268 - 283
	Actro YOU with Silent System	300 - 303
	Quadro YOU with Silent System	304 - 307
2	AvanTech YOU drawer	268 - 283
	Actro YOU with Silent System	300 - 303
	Quadro YOU with Silent System	304 - 307


AvanTech YOU double walled drawer system

► Example application with tall unit



- For individual cabinet body heights and widths
- Optimum use of storage space
- Recommended cabinet body widths 300 – 600 mm
- Other configurations are also possible

Example application




No.	Application	see pages
1	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
2	AvanTech YOU drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 300 - 303 304 - 307
3	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
4	AvanTech YOU drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 300 - 303 304 - 307

AvanTech YOU double walled drawer system


► Example application for pantry



- For individual cabinet body heights and widths
- Optimum use of storage space
- Recommended cabinet body widths: 450 – 1200 mm, with 2 hinged doors for cabinet bodies wider than 600 mm
- Recommended hinge: Sensys 8657i fast assembly concealed hinge
- Other configurations are also possible



Example application



No.	Application	see pages
1	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
2	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
3	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
4	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
5	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307
6	AvanTech YOU internal drawer Actro YOU with Silent System Quadro YOU with Silent System	268 - 283 / 290 - 293 300 - 303 304 - 307


AvanTech YOU double walled drawer system

► Example application on a drawer with bottom cutout



- For use of space under the sink
- Other configurations are also possible

Example application






No.	Application	see pages
1	AvanTech YOU drawer side profile, left and right	271 - 272
2	AvanTech YOU Design profile, 4 pieces	271
3	AvanTech YOU drawer front connector, 4 pieces	272
8	AvanTech YOU connector for rear panel, 2 pieces on left and on right	288
9	AvanTech YOU rear panel profile for cut to length, or C wooden back panel	288
11	Actro YOU / Quadro YOU drawer runner with Silent System	299 - 307
A	Front	
B	Bottom (material thickness 16 mm)	
C	Wooden back panel (material thickness 16 mm)	

AvanTech YOU double walled drawer system



► Example application on a drawer with bottom cutout

Planning / installation dimensions



* All dimensions identical for Actro YOU and Quadro YOU

Example with height 101



BB Bottom panel width	KB Cabinet body width	NL Nominal length	LB Clear inside width
BL Bottom panel length	RB Rear panel width	KD Cabinet body side thicknesses	FB Front width

Dimension	mm
BL	NL - 21
BB	LB - 24
RB1	X1
RB2	X2
E	≥ 60
FB	B - X1 - X2 + 18